

RECOMMENDED OVEN TEMPERATURES

<u>MATERIAL</u>	<u>FAHRENHEIT</u> <u>Minimum-Maximum</u>	<u>CELCIUS</u> <u>Minimum-Maximum</u>
Duraflex™	200-250	Blistering In A Frame
	300-350	Draping With A Seam
	260-300	For Inner Boot
ProFlex-S(with Silicone)	300-350	Blistering In A Frame
	300-350	Draping With A Seam
Modified Polyethylene	350-375	
Low Density Polyethylene	350-375	177-190
High Density Polyethylene	350-375	177-190
Polypropylene (Including Colors)	350-375	177-190
Co-Polymer (Including Colors)	350-375	177-190
Vivak® (Durr-Plex)	325-350	163-177
DuraFoam™	325-350	163-177
FootForm (Alternate to Subortholen®)	350-375	177-190
Plastazote	325-350	163-177
Performa Plus	325-370	165-185